

Berghof(독일) High Pressure Reactor

고압반응기: HiPReactor

BR series: ~300°C, 200bar

용도: Synthesis(API), material testing, catalysis research

본체: 316Ti or Hastelloy

PTFE lining 으로 corrosive 조건 실험 가능.

BR-25(25ml) ~ BR-4000(5.7L)

With or Without PTFE insert

Stirring system: drive and stirrer
/magnetic stirrer

Sensor: Temperature, pressure

Sampling: Gas, Liquid

Heating / Thermostatic jacket

Lifting system or stand

Control: BRC, BR-HS



Berghof(독일) High Pressure Reactor

DAB Series

모델: DAB-2 / DAB-3 / DAB-3XXL
재질: 316Ti combination with PTFE insert
용량: 25~420 ml
Range: 250 °C, 200bar
Heating / Control system



DB Series

모델: DB-300 ~DB-2000
재질: 316Ti combination with PTFE insert
용량: 310~ 1880 ml
Range: 230 °C, 200bar
Pressure measurement: digital
Heating / Control system



NR Series

모델: NR-1500, 3000, 6000, 10000(11L)
재질: 316Ti or Hastelloy with PTFE insert
Range: 300 °C, 25bar
Stirring: Magnetic drive

